

BJT-120 Paste Labeling Machine



The design of this machine takes as the following, on the fan-shaped pole the rubber wheel attach a little sticking water then attach a tag after reaching the label driving place until it reaches the position of the paper wheel, then the not labeling claw take off the tag. At the same time it exchanges the tag to the vacuum attraction force it makes tags move to the label area attaching on the belt transmitting paper. Then attach on the bottle transmitted by the chain board. The action recycles and finishes the production process.

Specifications and Parameters

Max production capacity(Bottle/min): 40-60

Specification of Bottle(ml): 15-100

Voltage/Frequency(V/Hz): 220/50

Power(Kw): 1.5

Measurement of label(mm): (20-60)×(50-103)

Glue: White emulsion

All Measurement(mm): 1800×1150×1350

Weight(kg): 550



Pharmaceutical Equipment Specialists

35 Bridgegate Drv, Victoria Dock ,Hull, HU9 1SY, UK.

tel: +44 1482 225628 fax : +44 8082089525

e mail: gorclark@gmail.com web: www.nevos.co.uk