



Pharmaceutical Equipment Specialists

35 Bridgegate Drv, Victoria Dock, Hull, HU9 1SY, UK. tel: +44 1482 225628 fax : +44 8082089525

e mail: gorclark@gmail.com **web:** www.nevos.co.uk

BZ-120 I Super-speed Bottle-regulating Machine



This machine is applied mostly in pharmaceutical companies to put bottles in order automatically. It can also be used to assist assembly line for chemical, light or food industry.

It is easy to operation is also simple. It is reliable and widely applicable.

B. There is equipment to test quantity of each bottle and to protect in case of over loading.

C. The surface and inside body are both made up of stainless steel of high quality, with a beautiful outlook, applying to GMP standard.

D. Bottle couector and closed cover of machine can be fitted as required, improving production efficiency greatly.

Specifications and Parameters

Max production capacity(Bottle/min) 60-150

Specification of Bottle(ml) 15-150

Voltage/Frequency(V/Hz) 220/50

Power(Kw) 1

All Measurement(mm) 1000*1150*1230

Weight(kg) 250