

## KF01-B Electromagnetic Sensitive Sealing Machine



KF electrical-magnetic sensitive aluminum foil sealing is suitable for diverse load tailoring to a wide range. Also able to trace adjustment export. In unfavorable circumstances, for instance, scattered with powder, oil lipids, water gels, and various interference, it also can perform sealing validly with such traits as highly reliability, operation at ease, long shell-life, and ability to meet the GMP's debugging requirements. It is a high-tech product in a combination of electromechanical photo know-how, in April, 1998, after being reviewed by the Specialist Committee, it is ranked unanimously the leading level domestically and it wins the No.1 for sale promotion among the same type of products.

- A. Using the advanced theory, electric appliances. It is easy to operate.
- B. There is the feed back of double-shutting of the main back track stable in property.
- C. This machine has the equipment about counting and pulling out the no aluminium foil.
- D. According to the size of yield. And regulating the electric current, voltage can control to.

### Specifications and Parameters

Max production capacity(Bottle/min): 60-180

Specification of Bottle(ml): 15-200

Voltage/Frequency(V/Hz): 220/50

Power(Kw): 2-3

Measurement(mm): 1600×500×1000

Measurement(Leng/width/Height)(mm): 15-45/35-300

Weight(kg): 80



*Pharmaceutical Equipment Specialists*

35 Bridgegate Drv, Victoria Dock, Hull, HU9 1SY, UK. tel: +44 1482 225628 fax : +44 8082089525

e mail: [gorclark@gmail.com](mailto:gorclark@gmail.com) web: [www.nevos.co.uk](http://www.nevos.co.uk)